



# SAGA


Sagittal Alignment System





### Hyperlordotic Cage

	30° A x B	40° A x B
	17x20mm	20x20mm
	17x25mm	20x25mm
	17x30mm	20x30mm
	18x20mm	24x25mm
	18x25mm	24x30mm
	18x30mm	



### Anterior Intersomatic Cage Screw

Ø x Length
4,5 x 25mm
4,5 x 30mm
4,5 x 35mm
4,5 x 40mm

#### Correlation

30°		40°	
Cage	Cylinder	Cage	Cylinder
17x20mm	M8 x 21mm	20x20mm	M8 x 21mm
17x25mm	M9 x 27mm	20x25mm	M9 x 27mm
17x30mm	M10 x 33mm	20x30mm	M10 x 33mm
18x20mm	M8 x 21mm	24x25mm	M9 x 27mm
18x25mm	M9 x 27mm	24x30mm	M10 x 33mm
18x30mm	M10 x 33mm		



### Instrumentals



T-Cable with Quick Hitch



Handle Ratchet 1/4 "Square Drive"



Distract Clamp



Spacer for Cage  
08mm | 12mm | 16mm  
10mm | 14mm



Proof and Cage Extractor



2.5mm Hex Cardan Wrench with Quick Hitch



Thread Protector  
M8 | M9 | M10



Hex Key  
2.5mm | 4.5mm



Cylinder Trefina  
M8 | M9 | M10



Cardan Hole Initiator



Introducer to Cage



Proof for Cage  
30° and 40°